

PRODUCT DATA SHEET

AMBERJET™ I 600 H

Industrial Grade High Capacity Gel Cation Exchange Resin

AMBERJET 1600 H resin is a uniform particle size, gel type, strong acid cation exchange resin with a combination of very high capacity and stability that enables a completely new level of performance in ion exchange applications. It is intended for use in separable mixed bed systems which demand the ultimate in effluent purity, operating capacity, and resin life.


With a total capacity near **2.5 eq/L** in the H^+ form, AMBERJET 1600 H resin is especially well suited for condensate polishing in PWR nuclear or high pressure fossil electric generating plants. In this application, cation resin capacity controls the cycle throughput of the beds, and therefore the regeneration frequency. AMBERJET 1600 H resin can extend the hydrogen cycle run length by as much as 20% beyond any currently available resin, and this proportionally reduces the number of regenerations and effort needed to operate the condensate polishing plant. The exceptionally good backwash separation characteristics of AMBERJET 1600 H resin further simplify the regeneration process.

Due to its very high level of DVB crosslinker, AMBERJET 1600 H resin possesses the best physical stability and oxidative stability of any commercially available cation resin, either gel or macroporous. This allows for maximum useful life of the cation resin, while at the same time minimising the release of organic sulfonate leachables.

The low leachables characteristic of AMBERJET 1600 H resin helps to preserve the kinetic response of the anion exchange resin in the mixed bed, thus allowing for reduced levels of sulphate in the steam generator or boiler, which is especially critical in PWR plants where organic amines are used.

HIGH OPERATING CAPACITY

Figure 1 shows the expected hydrogen cycle operating capacity for AMBERJET 1600 H resin compared to other cation resins which have been widely used in condensate polishing applications. Due to its exceptionally high available capacity, the operating capacity of AMBERJET 1600 H resin increases dramatically compared to conventional cation resins, when more regenerant acid is applied.



PROPERTIES

Physical form _____
 Matrix _____
 Functional group _____
 Ionic form as shipped _____
 Conversion to H^+ form ^[1] _____
 Total exchange capacity ^[1] _____
 Moisture holding capacity ^[1] _____
 Shipping weight _____
 Specific gravity _____
 Particle size _____
 Uniformity coefficient ^[1] _____
 Harmonic mean size ^[1] _____
 < 0.425 mm ^[1] _____
 Maximum reversible swelling _____

Dark amber translucent spherical beads
 Polystyrene divinylbenzene copolymer
 Sulfonic acid
 H^+ form
 99 % minimum
 ≥ 2.40 eq/L (H^+ form)
 37 to 43 % (H^+ form)
 840 g/L
 1.28 (H^+ form)
 ≤ 1.2
 0.60 to 0.70 mm
 0.5% max
 $Na^+ \rightarrow H^+ \leq 4 \%$

^[1] Contractual value

Test methods are available on request.

SUGGESTED OPERATING CONDITIONS

Maximum operation temperature _____	135 °C
Minimum bed depth _____	800 mm
Service flow rate (Linear Velocity) _____	10 to 120 BV*/h
Regeneration	
Regenerant _____	H₂SO₄ or HCl
Level (100% basis) _____	120 to 320 g/L
Concentration _____	4 to 8 %
Minimum contact time _____	30 minutes
Slow rinse volume _____	1 to 2 BV at regeneration flow rate
Fast rinse _____	4 to 8 BV



* 1 BV (Bed Volume) = 1 m³ solution per m³ resin

Transfer of mixed beds in condensate polishers: Take steps to minimise re-separation of mixed beds, including minimising the volume of free water or transfer water used. A remix is recommended in the service vessel before use.

HYDRAULIC CHARACTERISTICS

Figure 2 shows the bed expansion of AMBERJET 1600 H resin, as a function of backwash flow rate and water temperature. Figure 3 shows the pressure drop data for AMBERJET 1600 H resin, as a function of service flow rate and water temperature.

Pressure drop data are for clean, classified beds which have not accumulated solids during the service run. If the bed accumulates solids, the pressure drop would increase. The pressure drop of a mixed bed can be approximated by summing the component pressure drops.



LENNTECH

info@lenntech.com

www.lenntech.com

Tel. +31-15-261.09.00

Fax. +31-15-261.62.89

ROHM and HAAS 

AMBERJET is a trademark of Rohm and Haas Company and its affiliates, Philadelphia, U.S.A.

Ion exchange resins and polymeric adsorbents, as produced, contain by-products resulting from the manufacturing process. The user must determine the extent to which organic by-products must be removed for any particular use and establish techniques to assure that the appropriate level of purity is achieved for that use. The user must ensure compliance with all prudent safety standards and regulatory requirements governing the application. Except where specifically otherwise stated, Rohm and Haas Company does not recommend its ion exchange resins or polymeric adsorbents, as supplied, as being suitable or appropriately pure for any particular use. Consult your Rohm and Haas technical representative for further information. Acidic and basic regenerant solutions are corrosive and should be handled in a manner that will prevent eye and skin contact. Nitric acid and other strong oxidising agents can cause explosive type reactions when mixed with Ion Exchange resins. Proper design of process equipment to prevent rapid buildup of pressure is necessary if use of an oxidising agent such as nitric acid is contemplated. Before using strong oxidising agents in contact with Ion Exchange Resins, consult sources knowledgeable in the handling of these materials.

Rohm and Haas Company makes no warranties either expressed or implied as to the accuracy or appropriateness of these data and expressly excludes any liability upon Rohm and Haas arising out of its use. We recommend that the prospective users determine for themselves the suitability of Rohm and Haas materials and suggestions for any use prior to their adoption. Suggestions for uses of our products of the inclusion of descriptive material from patents and the citation of specific patents in this publication should not be understood as recommending the use of our products in violation of any patent or as permission or license to use any patents of the Rohm and Haas Company and its affiliates. Material Safety Data Sheets outlining the hazards and handling methods for our products are available on request.