

**DOW™ FILMTEC™ Membranes****DOW FILMTEC BW30FR-400 High Productivity Fouling Resistant RO Element****Features**

Designed to purify water with high biological or organic fouling potential in systems with well-controlled pretreatment, DOW™ FILMTEC™ BW30FR-400 reverse osmosis elements incorporate Dow's proprietary fouling resistant membrane technology that offers exceptional fouling resistance and cleanability. This product is an extension of the DOW FILMTEC BW30FR-365 element that has demonstrated its value for numerous customers around the world. The BW30FR-400 element features:


- High active area (400 square feet) for more productivity without increasing the operating flux.
- High rejection DOW FILMTEC RO membrane that has one of the widest pH cleaning ranges in the industry (pH 1-13) that allows for effective cleaning of scale, organic compounds and biofilm.
- Automated, precision fabrication with a greater number of shorter membrane leaves, reduces the overall effect of fouling and maximizes membrane efficiency.

These features offer system operators long-term efficiencies and trouble-free operation for RO membrane purification of fouling waters.

**Product Specifications**

| Product           | Part number | Active area<br>ft <sup>2</sup> (m <sup>2</sup> ) | Feed spacer<br>thickness (mil) | Permeate flow<br>rate gpd (m <sup>3</sup> /d) | Stabilized salt<br>rejection (%) | Minimum salt<br>rejection (%) |
|-------------------|-------------|--------------------------------------------------|--------------------------------|-----------------------------------------------|----------------------------------|-------------------------------|
| <b>BW30FR-400</b> | 202681      | 400 (37)                                         | 28                             | 10,500 (40)                                   | 99.5                             | 99.0                          |

1. Permeate flow and salt rejection based on the following standard conditions: 2,000 ppm NaCl, 225 psi (15.3 bar), 77°F (25°C), pH 8 and 15% recovery.
2. Flow rates for individual elements may vary but will be no more than 15% below the value shown.
3. Sales specifications may vary as design revisions take place.
4. Active area guaranteed +/-3%. Active area as stated by Dow FilmTec is not comparable to nominal membrane area often stated by some manufacturers. Measurement method described in Form No. 609-00434.

**Figure 1.**

| Dimensions – inches (mm) |              |            |           |
|--------------------------|--------------|------------|-----------|
| Product                  | A            | B          | C         |
| <b>BW30FR-400</b>        | 40.0 (1,016) | 1.125 (29) | 7.9 (201) |

1. Refer to Dow FilmTec Design Guidelines for multiple-element applications.
2. BW30FR-400 fits nominal 8-inch (203 mm) I.D. pressure vessel.

1 inch = 25.4 mm

## Operating Limits

- |                                                        |                               |
|--------------------------------------------------------|-------------------------------|
| • Membrane Type                                        | Polyamide Thin-Film Composite |
| • Maximum Operating Temperature <sup>a</sup>           | 113°F (45°C)                  |
| • Maximum Operating Pressure                           | 600 psig (41 bar)             |
| • Maximum Pressure Drop                                | 15 psig (1.0 bar)             |
| • pH Range, Continuous Operation <sup>a</sup>          | 2 - 11                        |
| • pH Range, Short-Term Cleaning (30 min.) <sup>b</sup> | 1 - 13                        |
| • Maximum Feed Silt Density Index                      | SDI 5                         |
| • Free Chlorine Tolerance <sup>c</sup>                 | <0.1 ppm                      |

<sup>a</sup> Maximum temperature for continuous operation above pH 10 is 95°F (35°C).

<sup>b</sup> Refer to Cleaning Guidelines in specification sheet 609-23010.

<sup>c</sup> Under certain conditions, the presence of free chlorine and other oxidizing agents will cause premature membrane failure. Since oxidation damage is not covered under warranty, Dow recommends removing residual free chlorine by pretreatment prior to membrane exposure. Please refer to technical bulletin 609-22010 for more information.

## Important Information

Proper start-up of reverse osmosis water treatment systems is essential to prepare the membranes for operating service and to prevent membrane damage due to overfeeding or hydraulic shock. Following the proper start-up sequence also helps ensure that system operating parameters conform to design specifications so that system water quality and productivity goals can be achieved.

Before initiating system start-up procedures, membrane pretreatment, loading of the membrane elements, instrument calibration and other system checks should be completed.

Please refer to the application information literature entitled "Start-Up Sequence" (Form No. 609-02077) for more information.

## Operation Guidelines

Avoid any abrupt pressure or cross-flow variations on the spiral elements during start-up, shutdown, cleaning or other sequences to prevent possible membrane damage. During start-up, a gradual change from a standstill to operating state is recommended as follows:

- Feed pressure should be increased gradually over a 30-60 second time frame.
- Cross-flow velocity at set operating point should be achieved gradually over 15-20 seconds.
- Permeate obtained from first hour of operation should be discarded.

## General Information

- Keep elements moist at all times after initial wetting.
- If operating limits and guidelines given in this bulletin are not strictly followed, the DOW™ FILMTEC™ Reverse Osmosis and Nanofiltration Three-Year Prorated Limited Warranty (Form No. 609-35010) will be null and void.
- To prevent biological growth during prolonged system shutdowns, it is recommended that membrane elements be immersed in a preservative solution.
- The customer is fully responsible for the effects of incompatible chemicals and lubricants on elements.
- Maximum pressure drop across an entire pressure vessel (housing) is 50 psi (3.4 bar).
- Avoid permeate-side backpressure at all times.

## Regulatory Note

These membranes may be subject to drinking water application restrictions in some countries: please check the application status before use and sale.

**FILMTEC™ Membranes**  
For more information contact:  
[info@lenntech.com](mailto:info@lenntech.com)  
[www.lenntech.com](http://www.lenntech.com)  
Tel. +31-15-261.09.00  
Fax. +31-15-261.62.89

Notice: The use of this product in and of itself does not necessarily guarantee the removal of cysts and pathogens from water. Effective cyst and pathogen reduction is dependent on the complete system design and on the operation and maintenance of the system.

Notice: No freedom from any patent owned by Dow or others is to be inferred. Because use conditions and applicable laws may differ from one location to another and may change with time, Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where Dow is represented. The claims made may not have been approved for use in all countries. Dow assumes no obligation or liability for the information in this document. References to "Dow" or the "Company" mean the Dow legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED.

