


AmberLite™ HPR2000 H Ion Exchange Resin

Uniform Particle Size, Macroporous, Strong Acid Cation Exchange Resin for Condensate Polishing and Mixed Bed Demineralization Applications for the Power Industry

Description

AmberLite™ HPR2000 H Ion Exchange Resin is intended for use in mixed bed polishing applications when highest resin purity and water quality are required. The very high level of DVB crosslinker, combined with a macroporous structure, offers exceptional physical and oxidative stability and sodium selectivity.



The exceptional physical and oxidative stability maximizes useful life of the cation resin. These properties also minimize the release of organic sulfonate leachables (TOC), helping to preserve the kinetic response of the anion exchange resin in the mixed bed, enabling lower levels of sulfate in the steam generator or boiler, which is especially critical in PWR plants where organic amines are used. The chemical stability also makes it especially suitable for high-temperature operation. The high sodium selectivity allows longest runtimes in amine cycle operation.

AmberLite™ HPR2000 H can operate reliably under the high flowrate and pressure drop conditions that are typically used in condensate polishers. The particle size and uniformity and color distinction of AmberLite™ HPR2000 H allow for excellent backwash separation when used in mixed beds with AmberLite™ HPR9000 OH Ion Exchange Resin, which offers excellent resistance to surface fouling. Together, these resins are known throughout the industry as a premium macroporous mixed bed resin pairing.

Resin Pairings

Recommended pairing:

- AmberLite™ HPR9000 OH Ion Exchange Resin (macroporous)

Additional options:

- AmberLite™ HPR550 OH Ion Exchange Resin (gel) – in external regeneration systems
- AmberLite™ HPR9000 SO₄ Ion Exchange Resin (macroporous)

Applications

- Mixed bed condensate polishing in PWR nuclear power plants
- Mixed bed condensate polishing in fossil power plants
- Condensate polishing in power plants operated with amine cycle
- Systems requiring exceptionally high osmotic stability

Historical Reference

AmberLite™ HPR2000 H Ion Exchange Resin has previously been sold as AMBERJET™ 2000 H Ion Exchange Resin.

Typical Properties

Physical Properties	
Copolymer	Styrene-divinylbenzene
Matrix	Macroporous
Type	Strong acid cation
Functional Group	Sulfonic acid
Physical Form	Gray to beige, opaque, spherical beads
Chemical Properties	
Ionic Form as Shipped	H ⁺
Total Exchange Capacity	≥ 1.7 eq/L (H ⁺ form)
Water Retention Capacity	51.0 – 56.0% (H ⁺ form)
Particle Size §	
Particle Diameter	950 ± 50 µm
Uniformity Coefficient	≤ 1.2
< 300 µm	≤ 0.3%
> 1180 µm	≤ 6.0%
Purity	
Metals, dry basis:	
Na	≤ 25 mg/kg
Fe	≤ 50 mg/kg
Cu	≤ 10 mg/kg
Stability	
Whole Uncracked Beads	≥ 95%
Friability:	
Average	≥ 350 g/bead
> 200 g/bead	≥ 95%
Swelling	Na ⁺ → H ⁺ ≤ 6%
Density	
Particle Density	1.18 g/mL
Shipping Weight	770 g/L

§ For additional particle size information, please refer to the [Particle Size Distribution Cross Reference Chart](#) (Form No. 45-D00954-en).

Suggested Operating Conditions

Temperature Range (H ⁺ form)	5 – 150°C (41 – 302°F)
pH Range (Stable)	0 – 14

For additional information regarding recommended minimum bed depth, operating conditions, and regeneration conditions for [mixed beds](#) (Form No. 45-D01127-en) or [separate beds](#) (Form No. 45-D01131-en) in water treatment, please refer to our Tech Facts.

Hydraulic Characteristics

Estimated bed expansion of AmberLite™ HPR2000 H Ion Exchange Resin as a function of backwash flowrate and temperature is shown in Figure 1.

Estimated pressure drop for AmberLite™ HPR2000 H as a function of service flowrate and temperature is shown in Figure 2. These pressure drop expectations are valid at the start of the service run with clean water.

Figure 1: Backwash Expansion

Temperature = 10 – 60°C (50 – 140°F)





Figure 2: Pressure Drop

Temperature = 10 – 60°C (50 – 140°F)



Product Stewardship

DuPont has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our product stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our product stewardship program rests with each and every individual involved with DuPont products—from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

Customer Notice

DuPont strongly encourages its customers to review both their manufacturing processes and their applications of DuPont products from the standpoint of human health and environmental quality to ensure that DuPont products are not used in ways for which they are not intended or tested. DuPont personnel are available to answer your questions and to provide reasonable technical support. DuPont product literature, including safety data sheets, should be consulted prior to use of DuPont products. Current safety data sheets are available from DuPont.

Please be aware of the following:

- **WARNING:** Oxidizing agents such as nitric acid attack organic ion exchange resins under certain conditions. This could lead to anything from slight resin degradation to a violent exothermic reaction (explosion). Before using strong oxidizing agents, consult sources knowledgeable in handling such materials.



info@lennotech.com Tel. +31-152-610-900
www.lennotech.com Fax. +31-152-616-289

All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. DuPont assumes no obligation or liability for the information in this document. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.

DuPont™, the DuPont Oval Logo, and all trademarks and service marks denoted with ™, ™, or ® are owned by affiliates of DuPont de Nemours Inc. unless otherwise noted. © 2020 DuPont.

