


AmberLite™ HPR4200 Cl Ion Exchange Resin

Uniform Particle Size, Gel, Strong Base Anion Exchange Resin for Industrial Demineralization Applications

Description

AmberLite™ HPR4200 Cl Ion Exchange Resin is a high-quality resin for use in industrial demineralization applications when high performance and cost-effective operation is required. The chemical properties and particle size of the resin have been balanced to combine excellent operating capacity with low pressure drop, while reducing chemical regenerant and rinse water usage.



AmberLite™ HPR4200 Cl is compatible with all system technologies; it has the flexibility to be used in lead single or layered anion bed and in mixed bed polishers, allowing users to inventory only one strong base anion resin for their demineralization needs. In mixed bed applications, the light color of this anion resin is designed to allow easy visual distinction from the dark-colored cation resin following backwash separation.

AmberLite™ HPR4200 Cl is designed for use in single bed or layered bed systems when paired with AmberLite™ HPR9600 or AmberLite™ HPR9500 Ion Exchange Resins.

In mixed bed applications AmberLite™ HPR4200 OH Ion Exchange Resin is recommended, but AmberLite™ HPR4200 Cl may be used if chloride-form is preferred by the user.

Resin Pairings

Recommended pairing in industrial demineralization applications:

- AmberLite™ HPR1200 H Ion Exchange Resin (gel) – for mixed bed
- AmberLite™ HPR1300 H Ion Exchange Resin (gel) – for mixed bed
- AmberLite™ HPR9500 Ion Exchange Resin (macroporous) – for layered bed
- AmberLite™ HPR9600 Ion Exchange Resin (macroporous) – for layered bed

Applications

- Demineralization
 - Ideally when treating water with:
 - High percentage of silica
 - When the treatment goal is:
 - Removal of strong and weak acids
 - Lowest silica leakage
- Mixed bed polishing

System Designs

Compatible with all system technologies and bed configurations:

- Mixed beds
- Packed beds
- Layered beds
- Counter-current / Hold-down
- Co-current

Historical Reference

AmberLite™ HPR4200 Cl Ion Exchange Resin has previously been sold as DOWEX MARATHON™ 4200 Cl Ion Exchange Resin.

Typical Properties

Physical Properties	
Copolymer	Styrene-divinylbenzene
Matrix	Gel
Type	Strong base anion, Type I
Functional Group	Trimethylammonium
Physical Form	Yellow, translucent, spherical beads
Chemical Properties	
Ionic Form as Shipped	Cl ⁻
Total Exchange Capacity	≥ 1.30 eq/L (Cl ⁻ form)
Water Retention Capacity	49.0 – 55.0% (Cl ⁻ form)
Particle Size §	
Particle Diameter	650 ± 50 µm
Uniformity Coefficient	≤ 1.25
< 300 µm	≤ 0.3%
> 850 µm	≤ 5.0%
Stability	
Whole Uncracked Beads	≥ 90%
Swelling	Cl ⁻ → OH ⁻ : 20%
Density	
Particle Density	1.07 g/mL
Shipping Weight	670 g/L

§ For additional particle size information, please refer to the [Particle Size Distribution Cross Reference Chart](#) (Form No. 45-D00954-en).

Suggested Operating Conditions

Temperature Range	
OH ⁻ form ‡	5 – 60°C (41 – 140°F)
Cl ⁻ form	5 – 100°C (41 – 212°F)
pH Range	
Service Cycle	1 – 14
Stable	0 – 14

‡ Operating at elevated temperatures, for example above 60 – 70°C (140 – 158°F), may impact resin life. Contact our technical representative for details.

For additional information regarding recommended minimum bed depth, operating conditions, and regeneration conditions for [mixed beds](#) (Form No. 45-D01127-en) or [separate beds](#) (Form No. 45-D01131-en) in water treatment, please refer to our Tech Facts.

Hydraulic Characteristics

Estimated bed expansion of AmberLite™ HPR4200 Cl Ion Exchange Resin as a function of backwash flowrate and temperature is shown in Figure 1.

Estimated pressure drop for AmberLite™ HPR4200 Cl as a function of service flowrate and temperature is shown in Figure 2. These pressure drop expectations are valid at the start of the service run with clean water.

Figure 1: Backwash Expansion

Temperature = 10 – 60°C (50 – 140°F)





Figure 2: Pressure Drop

Temperature = 10 – 60°C (50 – 140°F)



Product Stewardship

DuPont has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our product stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our product stewardship program rests with each and every individual involved with DuPont products—from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

Customer Notice

DuPont strongly encourages its customers to review both their manufacturing processes and their applications of DuPont products from the standpoint of human health and environmental quality to ensure that DuPont products are not used in ways for which they are not intended or tested. DuPont personnel are available to answer your questions and to provide reasonable technical support. DuPont product literature, including safety data sheets, should be consulted prior to use of DuPont products. Current safety data sheets are available from DuPont.

Please be aware of the following:

- **WARNING:** Oxidizing agents such as nitric acid attack organic ion exchange resins under certain conditions. This could lead to anything from slight resin degradation to a violent exothermic reaction (explosion). Before using strong oxidizing agents, consult sources knowledgeable in handling such materials.



info@lenntech.com Tel. +31-152-610-900
www.lenntech.com Fax. +31-152-616-289

All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. DuPont assumes no obligation or liability for the information in this document. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.

© 2020 DuPont. DuPont™, the DuPont Oval Logo, and all trademarks and service marks denoted with ™, SM or © are owned by affiliates of DuPont de Nemours Inc., unless otherwise noted.

DOWEX MARATHON™ is a trademark of The Dow Chemical Company used under license by DuPont.

