



FilmTec™ BW30 PRO-400/34i

High Rejection and High Performance Industry-Standard Brackish Water Reverse Osmosis Membrane Element

Key Features

- Delivers consistent water quality and higher rejection and flow than previous generation BW30 product
- Based on historical BW30 Industry-standard RO membrane with decades of proven performance
- Excellent durability resulting in stable, long-term performance
- Enhanced fouling protection thanks to 34 mil feed spacer
- Includes iLEC™ interlocking end caps, reducing system operating costs and the risk of o-ring leaks that can cause poor water quality

Key Applications


- Demineralization for industrial applications, such as: Power Generation, Steel & Metal, Chemical & Petrochemical
- Municipal water purification

Typical Properties

FilmTec™ Element	Active Area ft ² (m ²)	Feed Spacer Thickness (mil)	Permeate Flow Rate gpd (m ³ /d)	Stabilized Salt Rejection (%)	Minimum Salt Rejection (%)
BW30 PRO-400/34i	400 (37)	34	11,000 (42)	99.6	99.4

1. Permeate flow and salt rejection based on the following standard conditions: 2,000 ppm NaCl, 225 psi (15.5 bar), 77°F (25°C), pH 8 and 15% recovery.
2. Flow rates for individual elements may vary but will be no more than 15% below the value shown.
3. Sales specifications may vary as design revisions take place.

Element Dimensions



FilmTec™ Element BW30 PRO-400/34i Dimensions – inches (mm)	
A	40.0 (1,016)
B	40.5 (1,029)
C	7.9 (201)
D	1.125 ID (29)

1. For element weight information refer to [What is the weight of FilmTec™ elements as delivered?](#)
2. For element packaging and shipping information refer to [How are FilmTec™ elements packaged and shipped?](#)
3. Individual elements with iLEC™ Interlocking Endcaps measure 40.5 inches (1,029 mm) in length (B). The net length (A) of the elements when connected is 40.0 inches (1,016 mm).

Suggested Operating Conditions

Membrane Type	Polyamide Thin-Film Composite
Maximum Operating Temperature ¹	113°F (45°C)
Maximum Operating Pressure	600 psig (41 bar)
Maximum Pressure Drop	
Per Element	15 psig (1.0 bar)
Per Pressure Vessel (Minimum 4 Elements)	50 psig (3.5 bar)
pH Range	
Continuous Operation ¹	2 - 11
Short-Term Cleaning (30 min.) ²	1 - 13
Maximum Feed Flow ³	75 gpm (17 m ³ /hr)
Maximum Feed Silt Density Index	SDI 5
Free Chlorine Tolerance ⁴	< 0.1 ppm

1. Maximum temperature for continuous operation above pH 10 is 95°F (35°C).
2. Refer to [FilmTec™ Cleaning Guidelines](#) (Form No. 45-D01696-en).
3. For recommended feed and permeate flow rates, flux, and recovery for various feed sources, refer to [FilmTec™ Design Guidelines for multiple-element systems of 8-inch elements](#) (Form No. 45-D01695-en).
4. Oxidation damage is not covered under warranty, DuPont recommends removing residual free chlorine by pretreatment prior to membrane exposure. Please refer to [Dechlorinating Feedwater](#) (Form No. 45-D01569-en) for more information.

General Information

- Keep elements moist at all times after initial wetting.
- If operating limits and guidelines given in this bulletin are not strictly followed, the [FilmTec™ Reverse Osmosis and Nanofiltration Three-Year Prorated Limited Warranty](#) (Form No. 45-D00903-en) will be null and void.
- To prevent biological growth during prolonged system shutdowns, it is recommended that membrane elements be immersed in a preservative solution.
- The customer is fully responsible for the effects of incompatible chemicals and lubricants on elements.
- Avoid static permeate-side backpressure at all times.
- Permeate obtained from the first hour of operation should be discarded.
- The use of this product in and of itself does not necessarily guarantee the removal of cysts and pathogens from water. Effective cyst and pathogen reduction is dependent on the complete system design and on the operation and maintenance of the system.

Important Information

Please consider good operating practices for the optimal performance of the Reverse Osmosis membrane elements to assure damage free operation:

1. [Loading of Pressure Vessels - Preparation & Element Loading](#) (Form No. 45-D01602-en)
2. System Operation, including plant [Start-Up Sequence](#) (Form No. 45-D01609-en) and [RO & NF Systems Shutdown](#) (Form No. 45-D01613-en)
3. [Handling, Preservation, and Storage](#) (Form No. 45-D03716-en)

Full information of plant design, system operation and troubleshooting is given in the [FilmTec™ Reverse Osmosis Membranes Technical Manual](#) (Form No. 45-D01504-en).

Regulatory Note

This product may be subject to drinking water application restrictions in some countries; please check the application status before use and sale.



info@lenntech.com Tel. +31-152-610-900
www.lenntech.com Fax. +31-152-616-289



All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. DuPont assumes no obligation or liability for the information in this document. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.