




Pleated Polyethersulfone (PES) Membrane for Final Filtration of Wine & Beverages

"LOFMEM-B cartridges from Eaton are inherently hydrophilic and contain no added surfactants or wetting agents that could alter beverage taste. Perfect for processing beer, wine, bottled water, soft drinks and other beverages."

The polyethersulfone membrane provides high contaminant capacity, superior flow rates and consistent removal of particles and microorganisms. The cartridges are highly compatible with the most rigorous sanitizing methods in the beverage industry. Reliability is further assured with the LOFMEM-B's integrity testable design.

Features and Benefits

- Manufactured in an ISO Class 7 cleanroom environment
- 100% flushed with 18 MΩ-cm DI water and integrity tested
- Meets USP Class VI Biological Test for Plastics
- All materials are FDA listed for food and beverage contact

- Repeatably steamable and sanitizable
- High retention (LVR>7) of yeast and other spoilage organisms
- Pore size, lot and serial number are stamped on each filter element for identification and traceability

Filter Specifications

Media

Asymmetric polyethersulfone membrane

Inner core, end caps, cage
Polypropylene

Support layers
Spunbond Polypropylene

Gaskets/O-Rings
Buna-N, EPDM, Silicone, Viton, Teflon encapsulated Viton O-Rings

Micron ratings
0.2 µm, 0.45 µm, 0.65 µm

Dimensions / Parameters

Nominal lengths

9.75", 10", 20", 30", 40"
(24.7, 25.4, 50.8, 76.2, 101.6 cm)

Outside diameter

2.7" (6.9 cm)

Inside diameter

1.0" (2.54 cm)

Surface area

7.6 ft². (0.7m²) per 10 inch element

Max. sustained operating temperature

180°F (82°C) at 20 psid (1.38 bar)

Max. differential pressure

60 psid @ 80°F (4.14bar @ 27°C)
30 psid @ 160°F (2.07 bar @ 71°C)
15 psid @ 200°F (1.03 bar @ 93°C)

Max. reverse differential pressure

40 psid @ 70°F (2.76 bar @ 21°C)

Recommended change-out pressure

35 psid (2.4 bar)



Powering Business Worldwide™

Performance Specifications

Hot DI Water

Filter cartridge will withstand temperatures of 185°F (85°C) for up to 30 consecutive minutes.

Cleaning/Sanitization

Compatible with most common chemical cleaning, sanitizing and sterilizing agents and with pH range from 1–14. Consult factory for specific compatibility information.

Steam/Autoclave

Cartridges may be steamed or autoclaved for at least 50 half-hour cycles @ 275°F (135°C).

Typical Bacterial Retention Performance

Pore Size	Retention
0.2 µm:	LRV for <i>B. diminuta</i> ≥ 7.8
0.45 µm:	LRV for <i>S. marcescens</i> ≥ 8.5
0.65 µm:	LRV for <i>S. cerevisiae</i> ≥ 11 LRV for <i>L. brevis</i> ≥ 7.6

Integrity Test Specifications


Minimum Bubble Point values and maximum Diffusive Air Flow (per 10-inch cartridge) values for LOFMEM-B filters wet with water:

Pore Size	Bubble Point	Diffusive Air Flow
0.2 µm:	≥ 38psig (2.6 bar)	≤ 35cc/min @ 30psig (2.1 bar)
0.45 µm:	≥ 25psig (1.7 bar)	≤ 35cc/min @ 20psig (1.4 bar)
0.65 µm:	≥ 18psig (1.2 bar)	≤ 35cc/min @ 15psig (1.0 bar)


FDA Listed Materials

All materials comply with FDA title 21 of the Code of Federal Regulations Sections 174.5, as applicable for food and beverage contact.

LOFMEM-B Flow Rate (70°F / 21°C per 10" cartridge)



Filter Specification Code



©2009 Eaton Corporation. All Rights Reserved.
All trademarks and registered trademarks are the property of their respective owners. Litho USA

All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

LENNTECH

info@lennotech.com Tel. +31-152-610-900
www.lennotech.com Fax. +31-152-616-289

EATON

Powering Business Worldwide™

EF-LMB
8-2009