



MODULINE™

Multiple Single Bag Housing Assembly

*Designed for continuous
flow applications
and lower capital cost*

- Quick and easy bag changeout
- Flexibility for adding capacity
- Smaller footprint verses duplexed multibag housings
- Capital cost savings of 30% to 40% or more
- Each housing serviced individually
- No need to shut down system—continuous operation

The new MODULINE™ system provides a compact and efficient assembly of two or more single bag housing units. MODULINE can be equipped with the economical Flowline II™ housing for coarse particle filtration, the Sideline™ housing for a greater range of applications, or the most advanced Toplevel™ housings (shown above).

MODULINE is a space saving design that can be readily expanded with additional housing units and extra banks to provide the highest level of flexibility for your process requirements. The multi-vessel arrangement assures continuous flow rates. Each unit is individually valved and can be taken off-line in sequence for bag changeouts without having to take the complete bank of filters off line.



Powering Business Worldwide

Capital Cost Savings


Example - A duplexed four bag MBF in 316SS would cost between \$31K and \$35K, depending on the type of valves. A five station MODULINE would cost between \$21K and \$25K, a savings of up to 40%.

Specifications

- Two to eight housing units in each MODULENE assembly allows sequential bag changeout without system interruption
- Type 316 stainless steel construction for superior corrosion resistance (carbon steel and Type 304SS construction are options. Consult factory for correct model and availability)
- Smooth bead blasted finish for easy cleaning
- Sized for #2 double-length bags (#1 size vessel assembly is optional)
- Unique two-weld design
- Cover positively seals filter bag (Topline, Sideline)
- Buna N™ seals standard (Topline)
- Stainless steel basket
- Domed cover with swing bolts (Topline)
- Integrated ergonomic cover handle with swing bolts (Flowline II, Sideline)
- ASME code stamp (Topline, Sideline)
- Optional gauges, vents and pressurize air port with 1/4" NPT threaded cover taps
- Easy-action 1/4-turn ball valves for precision flow control

Dimensions for MODULENE using Topline Vessels.

Details on MODULENE assemblies using Sideline and Flowline II vessels available on request.



MODULENE Systems with Topline housings

Item Number	No. of Bags	Bag Size	gpm @ 2.1 psid	Volume (gal.)	Weight (lbs.)	Max pressure (psid*)	Max temp (°F)	I/O connection	A	B	C	D	E
F3AVTB0402	2	2	140	16.5	320	150	400	3"	24"	23"	7-3/4"	24-3/16"	47-1/2"
F3AVTB0403	3	2	210	25.7	490	150	400	4"	36"	35"	8-1/4"	24-11/16"	48"
F3AVTB0404	4	2	280	35	630	150	400	4"	48"	47"	8-1/4"	24-11/16"	48"
F3AVTB0405	5	2	350	54.2	800	150	400	6"	60"	59"	9-15/16"	25-3/4"	49-1/16"
F3AVTB0406	6	2	420	65.5	950	150	400	6"	72"	71"	9-15/16"	25-3/4"	49-1/16"
F3AVTB0407	7	2	490	76.7	1100	150	400	6"	84"	83"	9-15/16"	25-3/4"	49-1/16"
F3AVTB0408	8	2	560	86	1250	150	400	6"	96"	95"	9-15/16"	25-3/4"	49-1/16"

*psid values are without filter media.

Dimensions vary by model

©2010 Eaton Corporation. All Rights Reserved.
All trademarks and registered trademarks are the property of their respective owners. Litho USA

All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.