

Membrane Element

SWC3+

Performance:	Permeate Flow:	7,000 gpd (26.5 m ³ /d)
	Salt Rejection:	
	nominal:	99.8 %
	minimum:	99.7 %

Type	Configuration:	Spiral Wound
	Membrane Polymer:	Composite Polyamide
	Nominal Membrane Area:	400 ft ²


Application Data*	Maximum Applied Pressure:	1200 psig (8.27 MPa)
	Maximum Chlorine Concentration:	< 0.1 PPM
	Maximum Operating Temperature:	113 °F (45 °C)
	Feedwater pH Range:	3.0 - 10.0
	Maximum Feedwater Turbidity:	1.0 NTU
	Maximum Feedwater SDI (15 mins):	5.0
	Maximum Feed Flow:	75 GPM (17.0 m ³ /h)
	Minimum Ratio of Concentrate to Permeate Flow for any Element:	5:1
	Maximum Pressure Drop for Each Element:	10 psi

* The limitations shown here are for general use. The values may be more conservative for specific projects to ensure the best performance and longest life of the membrane.

Test Conditions

The stated performance is initial (data taken after 30 minutes of operation), based on the following conditions:

32,000 ppm NaCl
800 psi (5.5 MPa) Applied Pressure
77 °F (25 °C) Operating Temperature
10% Permeate Recovery
6.5 - 7.0 pH Range



A, inches (mm)	B, inches (mm)	C, inches (mm)	Weight, lbs. (kg)
40.0 (1016)	7.95 (201.9)	1.125 (28.6)	36 (16.4)

Notice: Permeate flow for individual elements may vary + or - 15 percent. All membrane elements are supplied with a brine seal, interconnector, and o-rings. Elements are vacuum sealed in a polyethylene bag containing less than 1.0% sodium meta-bisulfite solution, and then packaged in a cardboard box.

Hydranautics believes the information and data contained herein to be accurate and useful. The information and data are offered in good faith, but without guarantee, as conditions and methods of use of our products are beyond our control. Hydranautics assumes no liability for results obtained or damages incurred through the application of the presented information and data. It is the user's responsibility to determine the appropriateness of Hydranautics' products for the user's specific end uses. 6/29/05

LENNTECH

info@lenntech.com

www.lenntech.com

Tel. +31-15-261.09.00

Fax. +31-15-261.62.89