

PRODUCT INFORMATION

LEWATIT® S 4328



Lewatit® S 4328 is a macroporous anion exchange resin of medium basicity containing tertiary and quaternary amino groups, based on polystyrene. It is bead-shaped and has a special bead size distribution for use in the following processes:

- » Lewatit® WS system (fluidized bed)
- » Lewatit® VWS system (compound fluidized bed)
- » Standard co current regenerated system

On account of its high total capacity, good chemical stability and osmotic properties, **Lewatit® S 4328** is suitable in the free base form for:

- » removal of acid and simultaneous decolorisation of solutions of organic substances, e.g. sugar, gelatine, glycerin, grape must, whey, fruit concentrates, etc.

The macroporous structure and the balanced relation between the weakly and strongly basic groups ensures very good adsorption of organic substances (e.g. colorants) and partial adsorption of organic acids and mineral acids. The substances adsorbed are easy to desorb by regeneration with caustic soda solution.

Lewatit® S 4368 complies with current German legislation on food and food-contact uses and is chemically in compliance with the FDA regulations FCN 55.

Lewatit® S 4368 is in compliance with the European Resolution ResAP (2004)3 (superseding the former Resolution AP (97)1) with regard to Total Organic Carbon (TOC) release according to the AFNOR test T 90-601.

When using **Lewatit® S 4368** to treat potable water and the aqueous solutions listed above, special care should be given to the initial cycles of the new resin. Please refer to the recommended start-up conditions in this data sheet.

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess, Business Unit Ion Exchange Resins.

PRODUCT INFORMATION

LEWATIT® S 4328



General Description

Ionic form as shipped	free base/Cl ⁻
Functional group	tertiary/quaternary amine
Matrix	crosslinked polystyrene
Structure	macroporous
Appearance	beige, opaque

Physical and Chemical Properties

		metric units	
Uniformity coefficient*		max.	1.6
Bead size*	> 90 %	mm	0.4 - 1.25
Effective size*		mm	0.55 (+/- 0.05)
Bulk density	(+/- 5 %)	g/l	620
Density		approx. g/ml	1.03
Water retention		wt. %	57 - 63
Total capacity*		min. eq/l	1.4
Volume change	total swelling (delivered --> Cl ⁻)	typical vol. %	22
Volume change	operational swelling	typical vol. %	12
Stability	at pH-range		0 - 14
Storability	of the product	max. years	2
Storability	temperature range	°C	-20 - 40

* Specification values subjected to continuous monitoring.

Recommended Start-up Conditions*

(in drinking water and food applications only)

Linear velocity	approx. m/h	5
Rinse water requirement	approx. BV	20

PRODUCT INFORMATION

LEWATIT® S 4328



Recommended Operating Conditions*

		metric units	
Operating temperature		max. °C	70
Operating pH-range			0 - 8
Bed depth		min. mm	800
Specific pressure loss	(15 °C)	approx. kPa*h/m ²	1.1
Pressure loss		max. kPa	250
Linear velocity	exhaustion	max. m/h	-
Linear velocity	backwash (20 °C)	approx. m/h	4 - 5
Bed expansion	(20 °C, per m/h)	approx. vol. %	17
Freeboard	backwash (extern / intern)	vol. %	80 - 100
Regenerant			NaOH
Counter current regeneration	level	approx. g/l	50 - 80
Counter current regeneration	concentration	wt. %	2 - 4
Co current regeneration	level	approx. g/l	50 - 80
Co current regeneration	concentration	approx. wt. %	2 - 4
Linear velocity	regeneration	approx. m/h	5
Linear velocity	rinsing	approx. m/h	5 - 8
Rinse water requirement	slow / fast	approx. BV	6

* The recommended operating conditions refer to the use of the product under normal operating conditions. It is based on tests in pilot plants and data obtained from industrial applications. However, additional data are needed to calculate the resin volumes required for ion exchange units. These are to be found in our Technical Information Sheets.

PRODUCT INFORMATION

LEWATIT® S 4328

Additional Information & Regulations

Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

Toxicity

The safety data sheet must be observed. It contains additional data on product description, transport, storage, handling, safety and ecology.

Disposal

In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

Storage

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

The manner in which you use and the purpose to which you put and utilize our products, technical assistance and information (whether verbal, written or by way of production evaluations), including any suggested formulations and recommendations are beyond our control. Therefore, it is imperative that you test our products, technical assistance and information to determine to your own satisfaction whether they are suitable for your intended uses and applications. This application-specific analysis must at least include testing to determine suitability from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done by us. Unless we otherwise agree in writing, all products are sold strictly pursuant to the terms of our standard conditions of sale. All information and technical assistance is given without warranty or guarantee and is subject to change without notice. It is expressly understood and agreed that you assume and hereby expressly release us from all liability, in tort, contract or otherwise, incurred in connection with the use of our products, technical assistance, and information. Any statement or recommendation not contained herein is unauthorized and shall not bind us. Nothing herein shall be construed as a recommendation to use any product in conflict with patents covering any material or its use. No license is implied or in fact granted under the claims of any patent.

Edition: 2006-06-12
Previous Edition: 2005-10-19



WATER TREATMENT SOLUTIONS

info@lennotech.com Tel. +31-152-610-900

www.lennotech.com Fax. +31-152-616-289

For more information or a quote, please use the