



Water-Fine Series Filter Cartridges

DI and High Purity Water Filter

- Proprietary highly asymmetric polysulfone membrane media
- High purity polypropylene hardware
- Superior flow rates
- Long service life
- End configurations to fit most housings

Performance Specifications

Filter grades

0.05, 0.1, 0.2, 0.45, 0.65, 0.8, 1.2 μm

Maximum differential pressure

5.5 bard (80 psid) @ 20°C (68°F)

1.4 bard (20 psid) @ 95°C (203°F)

Recommended change-out differential pressure¹

35 psid (2.4 bard)

Food and water contact use

Please contact Pall Corporation to verify that the product conforms to your national legislation and/or regional regulatory requirements for water and food contact use.

Sanitizing agents

Cartridge may be sanitized in place with common oxidizing agents. Consult Pall for compatibility information.

Rinse-up

Cartridges will rinse-up to 18 Megohm-cm with a minimum of throughput.


Pre-rinsing

A pre-rinse is available upon request. Specify code 314 at the end of part number. See page 2.

Product Specifications

Materials of construction

Filter media:	Highly asymmetric polysulfone membrane
Support material:	Polypropylene
Hardware:	Polypropylene
Surface treatment:	Hydroxypropylcellulose
Sealing:	Thermal bond
Gaskets/O-rings:	Silicone elastomer, EPDM, nitrile, fluorocarbon elastomer, FEP encapsulated silicone



Dimensions (nominal)

Outside diameter: 6.6 cm (2.6 in)

Lengths: 10.2 cm (4 in), 24.8 cm (9.75 in),
25.4 cm (10 in), 49.5 cm (19.5 in),
50.8 cm (20 in), 74.3 cm (29.25 in),
76.2 cm (30 in), 99.1 cm (39 in),
102 cm (40 in)

Product Applications

- Pre and post filter for DI water
- Point-of-use filter for DI water
- Filtration of aqueous chemical solutions

¹ Provided that the maximum differential pressure is not exceeded based on the temperature limits defined above.

Liquid Flow Specifications

Filter grade (µm)	DI water flow (25.4 cm/10 in equivalent)	
	lpm/mbard	gpm/psid
0.05	0.05	1.0
0.1	0.09	1.7
0.2	0.16	3.0
0.45	0.30	5.5
0.65	0.33	6.0
0.8	0.38	7.0
1.2	0.44	8.0

Ordering Information

Pall Part Number = WFN 1 - 2 U 3 - 4 5

Table 1

Code	Filter grades (µm)
0.05	0.05
0.1	0.1
0.2	0.2
0.45	0.45
0.65	0.65
0.8	0.8
1.2	1.2

Table 2

Code	Cartridge lengths (nominal) cm/in
4	10.2/4
9.75	24.8/9.75
10	25.4/10
19.5	49.5/19.5
20	50.8/20
29.25	74.3/29.25
30	76.2/30
39	99.1/39
40	102/40

Table 3

Code	Gasket/O-ring materials
S	Silicone (standard O-rings)
E	EPDM
V	Fluorocarbon elastomer
N	Nitrile (standard gaskets)
T	FEP encapsulated silicone
X	No O-ring required (M2 only)

Table 4

Code	End configurations
Blank	DOE with elastomer gasket seals & end caps
1X	DOE, 2.54 cm (1 inch) extended core
M2	SOE flat closed end fits housing with 020 O-ring post
M3	SOE flat closed end, external 222 O-rings (retrofits other manufacturers' Code 0) ²
M5	DOE, internal 120 O-rings (retrofits 213 O-ring style) ²
M6	SOE flat closed end, external 226 O-rings (retrofits other manufacturers' Code 6) ²
M7	SOE fin end, external 226 O-rings (retrofits other manufacturers' Code 7) ²
M8	SOE fin end, external 222 O-rings (retrofits other manufacturers' Code 5) ²
M10	DOE, internal O-rings (fits other manufacturers' housings) ²
M11	SOE flat closed end, internal 120 O-ring (retrofits other manufacturers' X-style) ²
M20	SOE, internal O-ring (same as M10), closed end with deep recess

Table 5

Code	Pre-rinse options
Blank	No pre-rinse
314	Pre-rinse

² For details, contact Pall Corporation.



LENNTECH

info@lennotech.com

www.lennotech.com

Tel. +31-15-261.09.00

Fax. +31-15-261.62.89

Pall Corporation has offices and plants throughout the world. For Pall representatives in your area, please go to www.pall.com/contact.

Please contact Pall Corporation to verify that the product conforms to your national legislation and/or regional regulatory requirements for water and food contact use.

Because of technological developments related to the products, systems, and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2011, Pall Corporation. Pall and  are trademarks of Pall Corporation. * indicates a trademark registered in the USA. Filtration, Separation, Solution, and ENABLING A GREENER FUTURE are service marks of Pall Corporation.