



Marksman™ XLD Series Filter Elements

High Capacity Pleated Depth Polypropylene Filter Elements

- New, larger cartridge geometry
- Poly-Fine® Extended Life Depth (XLD) proprietary media for the innovative merger of depth and pleated technologies
- High surface area, high flow capacity
- Excellent retention of deformable contaminant
- Proprietary gel guard media
- Available to fit most Size 1 and Size 2 bag housings with no hardware changes
- Available in 101.6 cm (40 in) for use in unique 101.6 cm (40 in) Marksman housings
- Inside-out flow traps contaminant inside the element
- Quick, easy change-outs
- All polypropylene construction
- Short length option to accommodate shorter baskets



Performance Specifications

Filter grades

1.5, 3, 4.5, 10, 20, 30, 70 micron (µm)

Maximum operating differential pressure

Polypropylene

cage: to 5.2 bard @ 20°C (75 psid @ 68°F)
to 2.4 bard @ 74°C (35 psid @ 165°F)

NOTE: Stainless steel flange recommended for temperatures in excess of 43°C (110°F).

Recommended change-out differential pressure¹

2.4 bard @ up to 54°C (35 psid @ up to 130°F)

Food and water contact use

Please contact Pall Corporation to verify that the product conforms to your national legislation and/or regional regulatory requirements for water and food contact use.

Purity

Cartridges do not use surfactants, binders, and adhesives.

Sanitization

Contact Pall Corporation for assistance.

Product Specifications

Materials of construction

Filter media:	Polypropylene
Hardware:	Polypropylene
Support material:	Polypropylene
Gaskets:	EPDM, fluorocarbon elastomer, nitrile
Sealing:	Thermal bond

Dimensions (nominal)

Outside flange diameter:	Three diameters are available. Contact Pall for information on sizes.
Outside filter diameter:	15.2 cm (6 in)
Lengths:	Size 1 - Standard, Short Size 2 - Standard, Short, Extra Short Size 4 - 101.6 cm (40 in)

¹ Provided that the maximum differential pressure is not exceeded based on temperature limits defined above.

Particle Removal Ratings² (µm)

Cartridge Designation	90% Efficiency
XLDM 1.5	1
XLDM 3	3
XLDM 4.5	4
XLDM 10	6
XLDM 20	11
XLDM 30	17
XLDM 70	26

Typical Flow

Filter Grade	mbard/lpm (psid/gpm) Water @ 20°C (68°F)				
	Size 1	Size 2	40 in	Size 1 (short)	Size 2 (short)
1.5	0.929 (0.051)	0.401 (0.022)	0.255 (0.014)	1.038 (0.057)	0.474 (0.026)
3	0.364 (0.020)	0.164 (0.009)	0.109 (0.006)	0.401 (0.022)	0.200 (0.011)
4.5	0.218 (0.012)	0.091 (0.005)	0.054 (0.003)	0.237 (0.013)	0.109 (0.006)
10	0.146 (0.008)	0.054 (0.003)	0.036 (0.002)	0.164 (0.009)	0.073 (0.004)
20	0.054 (0.003)	0.018 (0.001)	0.018 (0.001)	0.054 (0.003)	0.018 (0.001)
30	0.073 (0.004)	0.036 (0.002)	0.018 (0.001)	0.073 (0.004)	0.036 (0.002)
70	0.091 (0.005)	0.036 (0.002)	0.018 (0.001)	0.109 (0.006)	0.036 (0.002)

NOTE: For kPa, multiply mbard/lpm by 0.1.

² Marksman XLD series filter cartridge retention ratings are based on Pall's Dynamic Efficiency test protocol. This single pass, destructive challenge test is based on ASTM F-795 test procedures for determining the performance of a filter medium. Fine test dust is used as the test contaminant for filters in the 1 to 20 micron range. Coarse test dust is used for micron ratings above 20 micron. Additional information can be obtained by contacting Pall Corporation.

³ Size 2 (only).

⁴ Select "XS" for Extra Short, "2" for Size 2 bag, and add "68" to the end of the part number (e.g., XLDMXS20-2UE-SFA 68).

⁵ For housings not listed or other than original equipment baskets, consult your Pall sales representative for proper flange/gasket style.

Ordering Information

Pall Part Number = XLDM 1 2 - 3 U 4 - 5 6

Table 1

Code	Short length option
Blank	Standard
S	Short
XS	Extra short ^{3, 4}

Table 2

Code	Filter grades (µm)
1.5	1.5
3	3
4.5	4.5
10	10
20	20
30	30
70	70

Table 5

Code	End configurations
PF	Plastic self-adjusting flange
SF	Stainless steel self-adjusting flange (required for temperatures >43°C/110°F)
NF	No flange (for use with reusable SS flange)

Table 6

Code	Flange/gasket styles ⁵
A ⁶	Rosedale ⁷ , Strainrite, Krystil Klear ⁸ , Pall
B	GAF ⁹ , FSI ¹⁰ side entry
C	FSI over the top, Hayward ¹¹ over the top

⁶ Requires "A" flange if using any of the Marksman 101.6 cm (40 in) products in the 101.6 cm (40 in) Pall Marksman housing.

⁷ Rosedale is a registered trademark of Rosedale Products, Inc.

⁸ Krystil Klear is a registered trademark of Pentair Water Filtration.

⁹ GAF is a registered trademark of GAF Corporation.

¹⁰ FSI is a registered trademark of Filter Specialists, Inc.

¹¹ Hayward is a registered trademark of Hayward Industrial Products, Inc.

Visit us on the Web at www.pall.com

Pall Corporation has offices and plants throughout the world. For Pall representatives in your area, please go to www.pall.com/contact.

Please contact Pall Corporation to verify that the product conforms to your national legislation and/or regional regulatory requirements for water and food contact use.

Because of technological developments related to the products, systems, and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2006, 2009, 2010, Pall Corporation. Pall, , Marksman, and Poly-Fine are trademarks of Pall Corporation. ® indicates a trademark registered in the USA. Filtration. Separation. Solution.SM is a service mark of Pall Corporation.

LENNTECH

info@lenntech.com

www.lenntech.com

Tel. +31-15-261.09.00

Fax. +31-15-261.62.89