

PENTEK® CHLORPLUS® SERIES CHLORAMINE REDUCTION CARTRIDGES

SUPERIOR CHLORINE AND CHLORAMINE REDUCTION



Pentair® Pentek ChlorPlus® carbon block cartridges help reduce sediment while providing greater chloramine performance capacities than granular carbon. They also significantly reduce the carbon fines found in many granular canisters.

The CRFC20-BB heavy duty radial flow cartridge measures 4.5" in diameter and 20" long, which is ideal for higher flow rate and capacity applications. This cartridge incorporates a 70-micron porous polypropylene outer shell and a spun polypropylene-wrapped core. The bed of granular activated carbon (GAC) between the outer shell and core creates a unique radial flow design which effectively removes chloramine, has a low pressure drop, and helps to reduce fines commonly seen in GAC-style cartridges.

All of these cartridges utilize advanced activated carbon technology which allows superior chloramine and chlorine reduction. The range of sizes and capacities offered makes them ideal for both point-of-entry (POE) and point-of-use (POU) applications.

FEATURES/BENEFITS

Superior chloramine and chlorine reduction

Unique design reduces carbon fines in filtered water

Ideal for POE or POU applications

Available in a variety of sizes

SPECIFICATIONS

ChlorPlus

Filter Media – Advanced bonded PAC

Endcaps – Polypropylene

Inner Wrap/Core – Polyolefin

Outer Wrap/Shell - Polyolefin

Netting – Polyethylene

Gaskets – Santoprene

Temperature Rating –
40-125°F (4.4-51.7°C)

CRFC-BB/CRFC20-BB

Filter Media – Advanced GAC

Endcaps – Polypropylene

Inner Wrap/Core – Spun polypropylene

Outer Wrap/Shell - Polyethylene

Post Filter - Spun polypropylene

Gaskets – Santoprene

Temperature Rating –
40-125°F (4.4-51.7°C)

SPECIFICATIONS AND PERFORMANCE

MODEL #	PART #	MAXIMUM DIMENSIONS	RATING (NOMINAL)*	INITIAL ΔP (PSI) @ FLOW RATE (GPM)*
ChlorPlus 10	255416-43	2.88" x 9.75" (73 mm x 248 mm)	1 micron	6 psi @ 1.0 gpm (0.41 bar @ 3.8 Lpm)
ChlorPlus 20	255417-43	2.88" x 20" (73 mm x 508 mm)	1 micron	6 psi @ 2 gpm (0.41 bar @ 7.6 Lpm)
ChlorPlus 10BB	355752-43	4.5" x 9.75" (114 mm x 248 mm)	1 micron	6 psi @ 2.0 gpm (0.41 bar @ 7.6 Lpm)
ChlorPlus 20BB	355753-43	4.5" x 20" (114 mm x 508 mm)	1 micron	6 psi @ 4.0 gpm (0.41 bar @ 15.2 Lpm)
CRFC-BB	355056-43	4.5" x 9.75" (114 mm x 248 mm)	25 micron	2.5 psi @ 2.5 gpm (0.17 bar @ 9.5 Lpm) <1 psi @ 1.5 gpm (<0.07 bar @ 5.7 Lpm)
CRFC20-BB	155967-43	4.5" x 20" (114 mm x 508 mm)	25 micron	2.5 psi @ 5 gpm (.17 bar @ 18.9 Lpm) <1 psi @ 2.5 gpm (<.07 bar @ 9.5 Lpm)

MODEL #	PART #	CHLORINE TASTE & ODOR REDUCTION @ FLOW RATE (GPM)*	CHLORAMINE REDUCTION @ FLOW RATE (GPM)*
ChlorPlus 10	255416-43	>50,000 gallons @ 1 gpm (>189,270L @ 3.8 Lpm)	2,500 gallons @ 0.5 gpm (9,463L @ 1.9 Lpm) 1,000 gallons @ 1.0 gpm (3,785L @ 3.8 Lpm)
ChlorPlus 20	255417-43	>100,000 gallons @ 2 gpm (>378,451L @ 7.6 Lpm)	5,000 gallons @ 1.0 gpm (18,927L @ 3.8 Lpm) 2,000 gallons @ 2.0 gpm (7,570L @ 7.6 Lpm)
ChlorPlus 10BB	355752-43	>250,000 gallons @ 2 gpm (>946,352L @ 7.6 Lpm)	3,500 gallons @ 2.0 gpm (13,249L @ 7.6 Lpm)
ChlorPlus 20BB	355753-43	>500,000 gallons @ 4 gpm (>1,892,706L @ 15.2 Lpm)	7,000 gallons @ 4.0 gpm (26,498L @ 15.2 Lpm)
CRFC-BB	355056-43	>100,000 gallons @ 2 gpm (>378,451L @ 7.6 Lpm)	12,000 gallons @ 1.5 gpm (45,424L @ 5.7 Lpm) 5,000 gallons @ 2.5 gpm (18,927L @ 9.5 Lpm)
CRFC20-BB	155967-43	>200,000 gallons @ 4 gpm (>757,082L @ 15.2 Lpm)	25,000 gallons @ 2.5 gpm (94,635L @ 9.5 Lpm) 10,000 gallons @ 5.0 gpm (37,854L @ 18.9 Lpm)

*Based on manufacturer's internal testing.

NOTES: Some harmless bacteria will attack cellulose media cartridges. If your cartridge seems to disintegrate, or has a musty or moldy odor, switch to a synthetic media cartridge or consult the manufacturer. Estimated capacity tested at given flow rate using 2 ppm free available chlorine to 0.5 ppm breakthrough and 3 ppm chloramine to 0.5 ppm breakthrough. Increased flow rates may result in less effective chlorine reduction.

WARNING: For drinking water applications, do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.



LENNTECH

info@lenntech.com Tel. +31-152-610-900

www.lenntech.com Fax. +31-152-616-289

All Pentair trademarks and logos are owned by Pentair, Inc. or its affiliates. All other registered and unregistered trademarks and logos are the property of their respective owners. Because we are continuously improving our products and services, Pentair reserves the right to change specifications without prior notice. Pentair is an equal opportunity employer.

310106 REV B MR14 © 2014 Pentair Residential Filtration, LLC All Rights Reserved.