

X-FLOW B 0125

CLASSIC ULTRAFILTRATION MEMBRANE

MEMBRANE DATASHEET

ARTICLE CODE: HD70600

BASIC CHARACTERISTICS

- Hydrophilic polysulfone tubular membrane cast on a composite polyester carrier
- Tubular membrane available in 14.4 mm
- Structure asymmetric
- Developed for use in a variety of ultrafiltration processes in industrial food and non-food applications
- Has a proven record of reliability in a wide range of processes

APPLICATIONS

- Concentration of modified starch waste water
- Manufacture of starch derivatives
- Production of whey protein concentrates
- Highly economical direct conversion of sour skimmed milk into quark
- Concentration of whole milk for cheese production
- Cost effective water removal from whole egg, egg white, fermented egg white and rinsing water
- Enzyme concentration
- Clarification of fruit juices

MEMBRANE COMPOSITION

- Membrane material composed of hydrophilic polysulfone
- Membrane carrier is a composite polyester woven/non-woven

PERFORMANCE DATA

Parameter	Unit	B 0125	Remarks
Initial flux	l/m ² .h 100 kPa	125 ± 25	RO-water at 25 °C
Transmembrane pressure	kPa	-20 .. + 1000	
Molecular weight cutoff	kDa	50	90% rej. on dextrans
pH		2 - 10	at 25 °C
Chlorine exposure	ppm.h	150000	at 25 °C
Temperature	°C	1 - 70	

Operation of membranes at any combination of maximum limits of pH, concentration, pressure or temperature, during cleaning or production, will severely influence the membrane lifetime.

SOLVENT RESISTANCE

Since the resistance of the membrane to solvents strongly depends on the actual process conditions, the indications given below should only be considered as guidelines.

Acids, pH > 2	+
Bases, pH < 11	+
Organic esters, ketones, ethers	--
Aliphatic alcohols	+
Aliphatic hydrocarbons	+
Halogenated hydrocarbons	--
Aromatic hydrocarbons	--
Polar organic solvents	--
Oils	+

X-FLOW B 0125

CLASSIC ULTRAFILTRATION MEMBRANE

MEMBRANE DATASHEET

CLEANING

Depending on the nature of the feed solution the following cleaning agents can be chosen:

Chemical	NaOCl (active chlorine)	500 ppm max.
	H ₂ O ₂	1000 ppm max.
	NaOH	pH ≤ 11 max.
	Nitric acid	pH ≥ 1
	Phosphoric acid	pH ≥ 1
	EDTA	pH ≤ 11
	Sodium tri-phosphate	
	Citric acid	
	Enzymatic compounds	

It is recommended to keep the pH between 1 and 11 and not to exceed a temperature of 40 °C during cleaning and/or disinfection.

If those standard cleaning techniques fail to remove the foulants, more concentrated cleaning solutions can be tried. Please contact X-Flow for recommendations.

It has to be stressed, however, that no warranty can be given on the efficiency of any cleaning nor on the membrane performance after such cleaning attempts.

STORAGE

New membrane modules can be stored as supplied.

Membrane modules should be stored in a dry, normally ventilated place, away from sources of heat, ignition and direct sunlight. Store between 0 and 40 °C.

The membrane modules should not be subjected to any freezing temperatures.

After use, UF membranes need to be stored wet at all times.

To avoid biological growth during shutdowns or storage, wet membranes should be treated with a compatible biocide. The membrane is compatible with many common disinfecting agents or biocidal preservatives. For short-term shutdowns, a daily flush with permeate quality water containing up to 2.0 ppm free available chlorine for 30 to 60 minutes may be adequate for bacteria control.

In case of long-term storage, membranes should be cleaned before the disinfection step is carried out. For disinfection, a 1% sodium metabisulfite solution can be used. In either situation, modules should be stored hydraulically filled.



X-FLOW BV

P.O. BOX 739, 7500 AS ENSCHEDE, NETHERLANDS WWW.X-FLOW.COM

Note: The information and data contained in this document are based on our general experience and are believed to be correct. They are given in good faith and are intended to provide a guideline for the selection and use of our products. Since the conditions under which our products may be used are beyond our control, this information does not imply any guarantee of final product performance and we cannot accept any liability with respect to the use of our products. The quality of our products is guaranteed under our conditions of sale. Existing industrial property rights must be observed.
DS CLAS B0125 E-3414 © 2014 Pentair, All Rights Reserved.

LENNTECH

info@lennotech.com Tel. +31-152-610-900

www.lennotech.com Fax. +31-152-616-289

