



Polygard® CE Filters

High-efficiency prefilters for removal of colloids from beverages

For 45 years, Millipore has assisted beverage companies throughout the world with perfecting manufacturing operations and developing microbial management concepts for monitoring and removing microorganisms. Taking from this experience, we have developed the Polygard CE filter to help with the critical needs in beverage manufacturing. Polygard CE is a pleated filter with composite glass fiber, inorganic filter aid and polypropylene media which provides unique characteristics useful in wine and some bottled water applications where difficult to remove colloidal particles present a challenge.

- ▶ Composite filter media for increased colloid retention capacity
- ▶ Ideal for protecting final membrane filters, or prefilters in "difficult" applications
- ▶ Conveniently fits all cartridge housings
- ▶ Resistant to backpressure
- ▶ Easy to clean and maintain
- ▶ Certificate of Compliance in each box

The unique media combination in the Polygard CE filter combines the high adsorption capacity of a glass microfiber and diatomite with the robustness of polypropylene for high resistance to backflush, peracetic acid, chlorine 100 ppm, and temperature. Polygard CE filters are available in a range of grades to retain colloidal matter better than any other prefilter cartridge. Use Polygard CE filters as:

- An alternative to Bevigard™ P and Bevigard M filters in protecting final Vitipore™ cartridge filters
- Protection for Bevigard P and Bevigard M filters

Application Characteristics

Polygard CE filters are engineered for high efficiency filtration giving extended protection to downstream final filters. Glass fibers with diatomaceous earth and polypropylene are fused into a composite filter medium to provide exceptional throughput and high colloidal retention capability. The Polygard CE filters can be repeatedly hot water regenerated providing highly cost effective filtration. They are supplied with a Certificate of Compliance, which certifies that Polygard CE filters meet quality assurance lot release criteria.




Use Polygard CE Filters in Your Beverage Production Processes

Wine Processing

-  Rinsed Bottle
-  Cap
-  Cap Conveyor
-  Bottle Conveyor
-  Filling Head
-  Microbial Enumeration (ME)
-  Rinse Water (RW)
-  Microbial Testing of Surfaces (MS)
-  Air Monitoring (AM)
-  Filterability Index (FI)

Polygard CE Filter




In wine processing, the Polygard CE filter has the role of protecting the final filter, ensuring a long life time and good economics, as well as a role of assuring the microbiological stabilization by reducing the initial bioburden.

Bottled Water Processing

-  Rinsed Bottle
-  Cap
-  Cap Conveyor
-  Bottle Conveyor
-  Filling Head
-  Point of Consumption
-  Microbial Enumeration (ME)
-  Rinse Water (RW)
-  Microbial Testing of Surfaces (MS)
-  Air Monitoring (AM)


Polygard CE Filter



During bottled water manufacturing, the Polygard CE filter protects the final filter to ensure a long life, provide good filtration train economics and minimize the risk of particulate and microbiological contamination.

Rugged Construction

Rugged, single-piece thermoplastic construction eliminates adhesives and minimizes extractables.



Certificate of Compliance


Each Polygard CE Filter package contains a Certificate of Compliance for documentation accuracy. This document certifies that the component materials meet FDA Indirect Food Additive requirements cited in 21 CFR 177–182 and that product was designed and manufactured to stringent specifications assuring its suitability for demanding beverage filtration applications

Specifications


	Per 10-inch Element Code 7	Code 0	Code F (excluding gasket)
Nominal Dimensions			
Diameter:	70 mm (2.75 in.)		
Overall length:			
10-inch cartridge:	319 mm (12.6 in.)	264 mm (10.4 in.)	246 mm (9.8 in.)
20-inch cartridge:	568 mm (22.4 in.)	512 mm (20.2 in.)	496 mm (19.6 in.)
30-inch cartridge:	816 mm (32.1 in.)	761 mm (30.0 in.)	746 mm (29.4 in.)
40-inch cartridge:	1062 mm (42.1 in.)	1011 mm (39.8 in.)	996 mm (39.2 in.)
Micron Retention Grades (Pore Size)	0.5, 1.0, 2.0 μ m		
Filtration Area			
0.5 μ m:	0.21 m ² (2.2 ft ²) per 10-inch element		
1.0 μ m:	0.30 m ² (3.2 ft ²) per 10-inch element		
2.0 μ m:	0.50 m ² (5.3 ft ²) per 10-inch element		
Materials of Construction			
Filter media:	Polypropylene, inorganic filter aid, glass fibers		
Structural components:	Polypropylene		
O-rings (Code 7):	Silicone		
Gasket (Code F):	Silicone		
Typical Operating Flow			
Wine applications:			
0.5 μ m:	800 – 1,000 litres per hour (200 – 260 gallons per hour) per 30-inch cartridge		
1.0 μ m:	1,000 – 1,200 litres per hour (250 – 310 gallons per hour) per 30 inch cartridge		
Water applications:			
0.5 μ m:	1,000 – 1,500 litres per hour (250 – 400 gallons per hour) per 30 inch cartridge		
Maximum Differential Pressure	4.8 bar (70 psid) at 20 °C (68 °F)		
Maximum Operating Temperature	80 °C (176 °F)		
Sterilization, Steam or Autoclave	121 °C, 5 cycles of 30 minutes		
Hot Water Sanitization	80 °C maximum for 30 minutes		
Indirect Food Additive	All component materials meet the FDA Indirect Food Additive requirements cited in 21 CFR 177-182.		

Typical Clean Water Flow Rates

Cartridge Filters with Polygard CE Media
— 10-inch



Cartridge Filters with Polygard CE Media
— 20-inch




Cartridge Legends Refers to Pore Size

CEA5 = 0.5 µm


CE01 = 1.0 µm

CE02 = 2.0 µm


Cartridge Filters with Polygard CE Media
— 30-inch



Cartridge Filters with Polygard CE Media
— 40-inch



Ordering Information



To Place an Order or Receive Technical Assistance

Millipore and Polygard are registered trademarks of Millipore Corporation.
Bevigard and Vitipore are trademarks of Millipore Corporation.
Lit. No. DS5623EN00 Rev. A 02/04 Printed in U.S.A. 04-096
© 2004 Millipore Corporation, Billerica, MA 01821 U.S.A. All rights reserved.

Yr{{crpu-0a

Rotterdamseweg 402m
2629HH Delft
The Netherlands
info@lenntech.com
www.lenntech.com
Tel. +31-15-261.09.00
Fax. +31-15-261.62.89

Polygard-CE-Filters

CEA501S06	CE0201S06
CEA501E06	CE0201E06
CEA502S06	CE0202S06
CEA502E06	CE0202E06
CEA503S06	CE0203S06
CEA503E06	CE0203E06
CEA504S06	CE0204S06
CEA504E06	CE0204E06
CEA571S06	CE0271S06
CEA571E06	CE0271E06
CEA572S06	CE0272S06
CEA572E06	CE0272E06
CEA573S06	CE0273S06
CEA573E06	CE0273E06
CEA574S06	CE0274S06
CEA574E06	CE0274E06
CEA5F1S06	CE02F1S06
CEA5F1E06	CE02F1E06
CEA5F2S06	CE02F2S06
CEA5F2E06	CE02F2E06
CEA5F3S06	CE02F3S06
CEA5F3E06	CE02F3E06
CEA5F4S06	CE02F4S06
CEA5F4E06	CE02F4E06
CE0101S06	
CE0101E06	
CE0102S06	
CE0102E06	
CE0103S06	
CE0103E06	
CE0104S06	
CE0104E06	
CE0171S06	
CE0171E06	
CE0172S06	
CE0172E06	
CE0173S06	
CE0173E06	
CE0174S06	
CE0174E06	
CE01F1S06	
CE01F1E06	
CE01F2S06	
CE01F2E06	
CE01F3S06	
CE01F3E06	
CE01F4S06	
CE01F4E06	