

## Water Technologies & Solutions fact sheet

# Hypersperse\* MDC759

## antiscalant / antifoulant

- Excellent results as a replacement for softener-filters
- Compatible with SoliSep\* MPT150 coagulant
- Highly effective over a wide-range of waters – For calcium-based and sulfate-based scales, notably, barium sulfate
- Compatible with all of the leading RO membranes
- Maintains cleaner membrane surfaces by inhibition and dispersing particulate foulants
- Effective over a wide pH range
- May be fed neat or diluted
- Compatible with feedwaters that contain aluminum and iron oxides

## description and use

Hypersperse\* MDC759 is a highly effective liquid antiscalant/antifoulant developed to control scale precipitates and reduce particulate fouling within membrane separation systems. This highly effective liquid antiscalant/antifoulant is formulated specifically to be used with SoliSep MPT150 coagulant. It is imperative that the coagulants used are compatible with the antiscalant/antifoulant being injected as incompatible chemicals may cause membrane fouling.

## application

For maximum effectiveness, Hypersperse MDC759 should be added prior to the static mixer or cartridge filter housing.

Maximum dilution of Hypersperse\* MDC759 is 10% with RO permeate or DI water.

## dosing

Typical dosage range is between 1 and 6 mg/L.

Please contact your local SUEZ representative to define the optimal feed point and dosage rate.

## Maximum Dilutions

Maximum dilution is temperature related as shown:

| Temperature | Maximum Dilution % |
|-------------|--------------------|
| <30°C       | 10                 |
| 30 – 35°C   | 25                 |
| >35°C       | 50                 |

## packaging information

Hypersperse MDC759 is a liquid material, available in a wide variety of customized containers and delivery methods. Contact your SUEZ sales representative for details.

## storage and handling

Keep from freezing.

## safety precautions

A Material Safety Data Sheet containing detailed information about this product is available on request.



info@lenntech.com Tel. +31-152-610-900  
www.lenntech.com Fax. +31-152-616-289