

New: XL-DER for Pure Dialysis Water

**EDI for Hemodialysis
Purifies Water & Removes Endotoxins**

Key Benefits Include:

- XL-DER EDI purifies RO water for central kidney dialysis systems
- XL-DER EDI removes endotoxins for healthier results
- XL-DER EDI is heat-sanitizable to 85°C



In kidney dialysis, the purity of water is critical in order to protect patients from harmful contaminants like endotoxins.

Endotoxins are byproducts of dead bacteria killed in the water purification system, and when not removed, may trigger fevers in patients. Since this water is in contact with a patient's own blood, it is critical to reduce endotoxins to the lowest possible level.

In a recent study in Japan, the use of Electropure™ XL-DER EDI further reduced endotoxin levels

(Continued on page 2)

coming from the RO by an additional 95%, study published in the Journal of Bioscience Control.

It is expected that UV-RO-EDI-UF will become the new standard for the preparation of best practices hemodialysis water.

EDI Module Parameters	Recommended for Optimum Performance	Maximum
Feedwater Conductivity Equivalent Including CO ₂ (See FCE calculation in Manual)	<9 µS/cm	<33 µS/cm
pH	7.0 to 7.5	5 to 9.5
Total Chlorine (as Cl ₂) and Ozone (O ₃)	ND	ND
Temperature	Operation: 5 to 45°C (40-113°F)	Sanitize: 72-85°C (162-185°F)
Dimensions (Width x Height x Depth)	22x56xD cm	(8.5x22xD in)
	XL-100-DER	XL-200-DER
Flow:	50-150 lph	100-300 lph
D, Depth:	17 cm (6.5 in)	19 cm (7.5 in)
Wt (kg/lb):	24kg/54lb	28kg/61lb
	XL-300-DER	XL-400-DER
	300-700 lph	0.7-1.5 m ³ /h
	26 cm (10 in)	29 cm (11.5 in)
	33kg/72lb	36kg/80lb
	XL-500-DER	
		1.3-2.5 m ³ /h
		37 cm (14.5 in)
		44kg/95lb

Electropure™ EDI Technology

- No concentrate recirculation or brine injection
- Thin-Cell efficient technology
- Thin-Concentrate non-scaling technology
- Unique non-scaling electrode system
- Patented Excellion™ membranes

Doing business with SnowPure

- Electropure™ EDI technology was born in 1977, before Ionpure
- SnowPure is privately held
- SnowPure is your partner, not a competitor
- High quality Electropure™ EDI training and OEM support

Benefits of Using EDI

- Continuous Process-no upsets
- Operating cost is minimized
- No hazardous waste, no associated costs and risks
- No regeneration acid or caustic
- Flexible—easy to expand a modular EDI system
- Reliable—no recirculation system components to fail

EDI Technology Training and OEM System Design Support

- SnowPure believes strongly in training—this helps ensure field success with Electropure™ EDI systems.
- SnowPure assists new OEM customers through their system design phase.
- Our customers also have access to our Best Practices P&ID's to aid in their EDI system optimization.
- Combined with ongoing Technical Service, we help ensure success.

SnowPure
High Technology Water

LENNTECH
WATER TREATMENT SOLUTIONS

info@lenntech.com Tel. +31-152-610-900
www.lenntech.com Fax. +31-152-616-289