

Industrial Ultrafiltration Spiral-Wound Element: **A6 (PVDF 500kDa)**

Synder Filtration's Ultrafiltration Elements offer an optimal combination of both flux and rejection in a comprehensive range of MWCO's. Contact us today to learn more about our complete line of membrane products and services.

RECOMMENDED OPERATING PARAMETERS

Membrane Type	
Proprietary PVDF or PES	Spiral-Wound with netted outerwrap or fiber glass hardshell (FRP)

Pressure	PSI	Bar
Max Inlet Pressure	116	8.0
Min Outlet Pressure	10	0.7
Max Differential Pressure per Element	18	1.2
Max Permeate Backpressure	5	0.3

Note: Soft start on boost pumps required to minimize pressure/flow shocks to elements.

Temperature	Fahrenheit	Celsius
Max. Operating	122°	50°
Max. CIP Temperature	122°	50°

pH Parameters	pH
pH Range during Operation at 25°C Max.	1.0-11.0
pH Range during CIP Operation at 50°C Max.	2.0-11.0

Peroxide	Max ppm.
Free Peroxide in Product During Operation	<3 ppm
Peroxide as a sanitizer at 25°C Max, pH6-7, 10minutes recirculation	0.1%

Chlorine	Norm ppm	Max ppm
Free Chlorine During Operation	0	<0.1
Chlorine During CIP at pH10.8-11.0 and 50°C	150	180

Note: Maximum chlorine exposure for all elements is 30 minutes per day at pH and temperature conditions listed above.

INDUSTRIAL SERIES BENEFITS

- Widest range of UF MWCO's available
- Good resistance to pH and temperature
- High resistance to fouling
- Customizable dimensions for unique housings



COMMON APPLICATIONS

- Anodic electrocoat paint
- Microbial/Particle removal

CONTACT US



LENNTECH

info@lennotech.com

www.lennotech.com

Tel.+31-152-610-900

Fax+31-152-616-289



DIMENSIONS & WEIGHT

Element	Model No.	Diameter (B) in (cm)	Length (A) in (cm)	PWT ID/OD in (cm)	Tube Extension (C) in (cm)	Dry Weight lb (kg)
1.8"	1812TM	1.8" (4.6)	11.75" (29.8)	0.665" (1.71)	0.75" (perm) 1.00" (plug)	1.0 (.45)
2.5"	2540TM	2.4" (6.1)	40.0" (101.6)	0.75" (1.90)	1.00" (2.54)	4.0 (1.8)
	2540HF	2.4" (6.1)	40.0" (101.6)	0.625" (1.59)	-	4.0 (1.8)
	2540HM	2.4" (6.1)	40.0" (101.6)	0.75" (1.90)	1.00" (2.54)	4.0 (1.8)
4"	4040TM	3.9" (9.9)	40.0" (101.6)	0.75" (1.90)	1.00" (2.54)	12.0 (5.5)
	4040HM	3.9" (9.9)	40.0" (101.6)	0.75" (1.90)	1.00" (2.54)	12.0 (5.5)
	4040HF	3.9" (9.9)	40.0" (101.6)	0.625" (1.59)	-	12.0 (5.5)
8"	7940HF	7.9" (20.1)	40.0" (101.6)	1.138" (2.89)	-	35.0 (15.9)
	8040HF	7.9" (20.1)	40.0" (101.6)	1.125" (2.86)	-	35.0 (15.9)


TECHNICAL NOTES

For element sizes not listed, please call or email Synder Filtration for details. We can design an element to fit your exact needs – just specify the element outer diameter (OD) or vessel/housing inner diameter (ID), element inner diameter (ID), and length. Elements are also available with or without a controlled bypass tail. Additional feed spacers are also available. Trials should be conducted to determine optimal application conditions.

Membrane Model → **V6 - 2 - 8040HF**

Spacer Size	Model No.
24 mil	1
31 mil	2
46 mil	3
65 mil	4
80 mil	5

Industrial Designations
T = Tape Wrapped
HM = Male
HF = Female



RECOMMENDED ELEMENT CROSS FLOW RATE

Element		Feed Spacer (in mils)				
		24	31	46	65	80
1.8"	m ³ /hr	0.7	0.8	0.9	1.0	1.1
	gpm	3	3	4	4	5
2.5"	m ³ /hr	1.3	1.5	1.8	2.0	2.1
	gpm	6	7	8	9	9
4.0"	m ³ /hr	3	4	5	5	5
	gpm	15	17	20	23	24
8"	m ³ /hr	15	17	20	23	24
	gpm	66	75	89	99	105

*Note: The recommended cross flow rate will be subject to differential pressure limitations and specific applications.

MEMBRANE AREA (SQ. FT)

Element		Feed Spacer (in mils)				
		24	31	46	65	80
1812TM		3.1	2.7	2.1	1.6	1.3
2540M		28	24	20	16	13
2540F		30	26	22	17	14
4040M		81	72	58	46	39
4040F		86	75	61	49	41
7940F		379	335	268	210	178
8040F		379	335	268	210	178

LENNTECH

info@lenntech.com Tel. +31-152-610-900
www.lenntech.com Fax. +31-152-616-289

